



Ophir Optronics Ltd.  
POB 45021 Jerusalem 91450 ISRAEL  
info@ophiropt.com www.co2optics.com  
Tel. 972-2-5484444 Fax 972-2-822338

**PRESS  
RELEASE**

## **CO2 Laser Optics Division of Ophir Optronics' Optics Group Announces Innovative Intra-Cavity MMR-P Mirror Coating**

Ophir's combined MMR-P and PLM-HR coatings represent a superior solution for multi-mirror cavity optics

**Jerusalem, Israel, 10 May 2011** – Ophir Optronics Ltd., a global leader in precision IR optics components and laser measurement equipment, announced today that the CO2 Laser Optics Division of its Optics Group has developed an innovative MMR-P coating for use in high-power CO2 laser systems based on multi-mirror cavity optics. The use of coatings like MMR-P is a cost-effective way to maximize reflection (>99.90% for S-Pol), improve performance, protect highly-sensitive mirror surfaces and prolong product life.

Ophir's OEM-approved MMR-P coating provides superior P reflection (>99.80%) and total random reflection (>99.85%) and is suitable for both Cu and Si mirrors. It is UV-resistant and allows for a phase shift tolerance of  $\pm 2@45^\circ$  and >70% reflection for 630-670nm, for superior cutting and cleaning capabilities.

"Our MMR-P coating can be used as total reflector or ZPS (TRZ) and allows for the highest total random reflection available," said Yehiel Plaut, Sales and Marketing Director for the CO2 Laser Optics Division of Ophir Optronics' Optics Group. "It can also be applied to a level-changing mirror in two-tiered resonator systems – a truly unique capability."



Si Mirror with MMR-P coating



Cu Mirror with MMR-P coating

## **About Ophir Optronics / Optics Group, CO2 Division**

Established in 1976, Ophir Optronics is a global leader in precision IR optics, laser measurement instrumentation and 3D non-contact measurement equipment.

Our CO2 Laser Optics Division produces a full range of OEM and replacement optics including beam-delivery and cavity optics as well as windows. Ophir provides the highest quality CO2 laser optics at the best price. The second largest OEM supplier in the world, all manufacturing is done in-house using automated CNC technology assuring complete uniformity. Driven by innovation, we've produced a longer lasting lens with a radioactive-free coating, called Black Magic™, and an ultra-low absorption lens with a transparent coating, called Clear Magic™. Our commitment to the customer is second to none, with a global distribution and support network. This unwavering commitment to forward thinking helps keep us "a cut above the rest". For more information, visit [www.co2optics.com](http://www.co2optics.com).

### **Contacts**

#### **Sales:**

Yehiel Plaut  
Sales & Marketing Director  
Optics Group, CO2 Laser Optics Division  
Ophir Optronics Ltd.  
Tel: +972-2-548-4592  
Email: [co2@ophiropt.com](mailto:co2@ophiropt.com)

#### **Media:**

Inbar Ben-Hur  
Optics Group Marcom Manager  
Ophir Optronics Ltd.  
Tel: +972-2-548-4383  
Email: [inbarb@ophiropt.com](mailto:inbarb@ophiropt.com)